









OKUMA

Axial Drilling and Milling Unit / Axial-Bohr-Fräseinheit

Motorizzato Assiale di Foratura e Fresatura / Unité de Perçage et de Fraisage Axiale

アキシアルドリルおよびミリングユニット

Lathe Angular Unit Twin • LAUT 60-1+1 A							SU-matic®	
Machine Types		Multus U3000 / U4000 / U5000 2S-W						
<div></div>								
#			 $n_1 : n_2$	i $n_1 : n_2$	$n_{2 \max}$	$T_{2 \max}$	#	
14801001230	ER 32	 100 bar	-	1 : 1	6'000 min ⁻¹	60 Nm		14430100040

Notes / Notizen / Note / Notes / メモ

Please check the machine strokes and the neighbor stations on potential overlaps - Bitte die Verfahrswege und die Nachbarstationen auf mögliche Überschneidungen überprüfen
 Si prega di verificare i percorsi e le stazioni adiacenti di potenziali sovrapposizioni - Vérifier les courses et qu'il n'y a pas de collisions possibles avec les stations voisines
 常に機械のストロークと、隣接するステーションにオーバーラップが無いを確認してください。
 Design data and dimensions subject to change - Konstruktions- und Massänderungen vorbehalten
 Cambiamento della costruzione e delle misure riservato - Droit de modification de structure et de cotes réservées
 設計仕様および寸法は通知することなく変更されます

www.su-matic.com • machining.su-matic@suhner.com • +41 56 464 29 90

Version: 27.08.2018

